

Power Generation Systems — The Right Septa Choice

AFA® – Pleated Backwashable Filter Elements

Graver's AFA non-precoatable backwashable condensate polishing septa are engineered to meet the high demands in the utility industry for iron oxide removal and repeated backwashing. A selection of filter media is available in absolute ratings ranging from 1.0 to over 20 microns to meet the removal requirements of each individual condensate system. Like all the condensate filters from Graver Technologies, a variety of end fittings can be selected to retrofit the elements in existing Powdex® or other condensate filter systems.

Features

- Absolute micron rating from 1 to 25 µm
- Removal efficiency rated at 99.9%
- High surface area of pleated media
- High dirt holding capacity
- Fixed pore construction eliminates dirt unloading as differential pressure increases



FILTER SPECIFICATIONS

Media	Polypropylene	
Inner Core	Polypropylene	Polypropylene
End Caps	Polypropylene	Polypropylene
Cage	Polypropylene	Polypropylene
Gaskets/O-Rings Options	EPDM Sulfur Free	
Micron Ratings	1.0, 3.0, 5.0, 10, 25µm	
	Other micron rated media available upon request	
Dimensions		
Nominal Lengths	50" (1,270 mm)	60" (1,524 mm)
	70" (1,778 mm)	80" (2,032 mm)
Outside Diameter	2½" (63.5 mm)	
Inside Diameter	1" (25.4 mm)	
Maximum Operating Temperature	Polypropylene: 180°F (85°C)	
Polypropylene Maximum	130 psid @ 70°F (8.9 bar @ 21°C)	
Collapse Pressure	40 psid @ 180°F (2.8 bar @ 85°C)	

FILTER REMOVAL EFFICIENCY


Beta Ratio	Beta 1,000	Beta 100	Beta 50
Efficiency	99.9%	99%	98%
Polypropylene			
1.0 micron	1.0	0.6	0.3
3.0 microns	3.0	2.0	1.5
5.0 microns	5.0	4.0	3.0
10.0 microns	10.0	8.0	7.0
25.0 microns	25.0	19.0	15.0

$$\text{Beta Ratio} = \frac{\text{Upstream particle counts}}{\text{Downstream particle counts}}$$


The micron ratings shown at various efficiency and beta ratio value levels were determined through laboratory testing, and can be used as a guide for selecting cartridges and estimating their performance. Under actual field conditions, results may vary somewhat from the values shown due to the variability of filtration parameters.

Testing was conducted using the multi-pass test method, water at 2.5gpm/10" cartridge. Contaminants included latex beads, coarse and fine test dust. Removal efficiencies were determined using dual laser source particle counters.

FLOW RATE VS PRESSURE DROP PER SQ. FOOT OF FILTER AREA POLYPROPYLENE FILTER @ 70°F (21°C)



Graver Technologies' Worldwide Locations



Superior Products & Global Reach

Graver is the global leader in high purity and condensate water treatment for power generation applications. Including both ion exchange and backwashable septa and filters.

Our innovative technology and products enable our customers to consistently meet today's tougher requirements for purity.

Graver's products treat more than 6.5 billion gallons of process water every day in over 38 countries. Over 75 percent of the nuclear powered generation plants, worldwide, use our technology. Graver has achieved this by consistently delivering dependable, high performance technology and products.

Whether your business is around the corner or around the world, Graver Technologies can support you with superior products and services.



ISO-9001 Factory in Glasgow, DE U.S.A.

For more information

Graver Technologies
 Customer Service:
800.533.6623
 E-mail: info@gravertech.com
 Website: www.gravertech.com

**United States
 Graver Technologies, LLC**

200 Lake Drive
 Glasgow, DE 19702 USA
 800.533.6623
 Phone: (302) 731.1700
 Fax: (302) 731.1707

**China
 Graver Technologies, LLC**

RM 16D, Bldg. B
 No.1118, Changshou RD
 Shanghai, China 200042
 Phone: (86) 21.5238.6576.608
 Fax: (86) 21.5238.6579

**Europe
 Graver Technologies, LLC**

Koenigstrasse, 10c
 D-70173 Stuttgart, Germany
 Phone: (49) 711.3154.7160
 Fax: (32) 61.32.9724



Graver Technologies

A member of The Marmon Group
 A Berkshire Hathaway Company

All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. AFA is a registered trademark of Graver Technologies.



ISO 9001:2000
 FM 38860