



# COAX<sup>®</sup> Series Filter Cartridges

## *Two Stage Depth Filter Cartridge*

### Product Specifications

**Media:** Thermally bonded Polypropylene/polyethylene fiber

**End Caps:**  
Polypropylene (when used)

**Gaskets/O-Rings:**  
Buna-N, EPDM, Santoprene, Silicone, Teflon Encapsulated Viton (O-Rings only), Viton

**Micron rating:**  
0.5, 1, 3, 5, 10, 25 µm

### Dimensions

**Nominal lengths:**  
5" 9.75" 10" 20" 30" 40"  
12.7 24.8 25.4 50.8 76.2 101.6 cm

**Outside diameter:** 2.6" (6.5 cm)

**Inside diameter:** 1.0" (2.54 cm)

### Operating Parameters

**Maximum operating temperature:** 140 °F (60°C)

**Maximum differential pressure:**  
100 psid @ 70°F (7 bar @ 21°C)  
2 psid @ 176°F (0.14 bar @ 80°C)

**Recommended change-out pressure:** 35 psid (2.4 bar)

The COAX Depth Filter cartridge is an integral two stage depth filter. The first stage is made of nonwoven melt blown polypropylene to trap coarser particles. The second stage is composed of a bicomponent polypropylene and polyethylene fiber to provide fine particle retention. This unique design provides a true graded, two zone structure that offers a marked increase in useful life and dirt capacity. In addition, the rigid nature means there is no flexing of the cartridge and greatly reducing media migration and particle unloading.

### FEATURES & BENEFITS

- Two stage depth filter
- Maximum dirt holding and useful life
- Inert pure polyolefin construction, non-shedding media
- Broad chemical compatibility
- Low extractables
- Extensive range of lengths and configurations
- Rigid construction resists unloading

### CERTIFICATIONS

- USP Class VI: Meets USP Class VI Biological Test for Plastics
- FDA Listed Materials: All materials comply with FDA Title 21 of the Code of Federal Regulations Sections 174.5, and 177.1520, as applicable for food and beverage contact.

### TYPICAL APPLICATIONS

- Paint
- Perfumes
- Cutting Oils
- CMP Slurries
- Magnetic Slurries
- Corn Syrup
- Plating Solutions
- Pre R.O.
- Coatings

### PERFORMANCE SPECIFICATIONS


- Sanitization:
  - Hot water at 176°F (80°C) at 5 psid (0.35 bar) for 30 min
  - In-line steam at 257°F (125°C) at 1 psid (0.07 bar) for 30 min
  - Autoclavable at 257°F (125°C) for 30 min

## COAX NOMENCLATURE INFORMATION

Filter Type	Retention Rating (microns)		Nominal Length (inches)		End Configuration		Gasket or O-Ring	
	0.5	5	-5	-20	P	Double Open End (Hard Endcaps)	B	Buna-N
COAX Series	1	10	-9.75	-30	P2	226/Flat Single Open End	E	EPDM
	3	25	-10	-40	P3	222/Flat Single Open End	N	None
					P7	226/Fin Single Open End	S	Silicone
				P8	222/Fin Single Open End	T	Teflon	
				PX	Extended Core		encap. Viton (O-Rings only)*	
				N	None			
				AM	Single Open End, Internal O-Ring	V	Viton	
<b>Example: COAX 25-40P3B</b>								
COAX	25		-40		P3			B

### COAX FLOW RATE

**Typical Flow Rate Clean Water at Ambient Temperature  
(per 10" cartridge)**



*For liquids other than water, multiply pressure drop by the fluid viscosity in centipoise*

### REMOVAL EFFICIENCY

Beta Ratio Efficiency	Beta 100 99%	Beta 20 95%	Beta 10 90%
0.5 µm	4.0	2.0	0.5
1 µm	8.0	3.0	1.0
3 µm	12.0	5.0	3.0
5 µm	20.0	8.0	5.0
10 µm	30.0	13.0	10.0
25 µm	50.0	30.0	25.0

$$\text{Beta Ratio} = \frac{\text{Upstream particle counts}}{\text{Downstream particle counts}}$$

#### FOR MORE INFORMATION

Customer Service/Technical Support: 1-888-353-0303  
 Europe (UK): +44-1424-777791 | China: +86-21-5238-6576  
 Asia: +65-9635-7690

GTX-264 3-19



#### DISTRIBUTED BY

All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believe to be reliable. However, It is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. COAX is a trademark of Graver Technologies, LLC.



Graver Technologies | 200 Lake Drive, Glasgow, DE 19702 | 302-731-1700 | 800-249-1990  
 Fax: 1-302-369-0938 | info@gravertech.com | www.gravertech.com

A member of The Marmon Group—A Berkshire Hathaway Company